



Index:

Index:	1
Introduction:.....	3
What's in the box?	3
Component overview:.....	4
Filters:	5
How to attach this matte box directly to your lens:	6
How to attach this matte box to 15mm rails:.....	7
Masks:.....	7
Optional hood extender:	8
Other accessories and configuration chart:	9

Introduction:

Thank you for purchasing a Vocas product. You are now the owner of a MB-260 matte box.

What's in the box?

Vocas MB-260 compact matte box 0200-0260

- 1 pc. Matte box MB-260 (0200-0260)
- 1 pc. Mask 125 wide 16:9 (0210-0010)
- 1 pc. Filter frame 4"x5,65" / 4"x4" (0210-0001)
- This manual

Vocas MB-260 Matte Box Kit for 15 mm LW Support 0260-2010


- 1 pc. Matte box MB-260 (0200-0260)
- 1 pc. Mask 125 wide 16:9 (0210-0010)
- 1 pc. Filter frame 4"x5,65" / 4"x4" (0210-0001)
- 1 pc. Height adjustable rails adapter (0360-0100)
- 1 pc. 114 mm Flexible donut ring (0250-0196)
- This manual

Vocas MB-260 Matte Box production Kit for 15 mm LW Support 0260-2011

- 1 pc. Matte box MB-260 (0200-0260)
- 1 pc. Mask 125 wide 16:9 (0210-0010)
- 1 pc. Filter frame 4"x5,65" / 4"x4" (0210-0001)
- 1 pc. Basic hood extender for MB-260 matte box (0200-0261)
- 1 pc. 114 mm Flexible donut ring (0250-0196)
- 1 pc. Mask kit 16:9 for MB-260 (0210-0020)
- 1 pc. 15 mm Swing away bracket for MB-260 (0460-06000)
- This manual


Component overview:

Matte box MB-260 (0200-0260):



Filters:

This matte box is capable of holding two 4"x4" or 4"x5,565" filters, one in the filter frame and one in the hood of the matte box.



How to attach this matte box directly to your lens:

The MB-260 can be attached directly to the front of your 114mm outside diameter lens or for smaller lenses by using either a step down ring (for lenses with a cylindrical lens front and without internal thread) or screw in type ring (for lenses with internal thread at the front). Please see our website for current available sizes.



Use the clip-on quick lock lever to clamp the matte box to the lens or ring. If the matte box closes to tight or to loose, use the Clip-on clamp adjustment knob to re-adjust the clamp mechanism.



How to attach this matte box to 15mm rails:

The MB-260 can be attached directly to 15mm LW standard rails by using a 15mm bars adapter (0360-0100) or a 15mm swing away bracket (0460-0600). Both of these adapters are adjustable in height.

For closing the gap between the opening in the matte box and you lens, our innovative Flexible donut ring (0250-0196) is highly recommended,



Masks:

The MB-260 comes standard with a 125mm 16:9 mask. This mask is suitable for most 24mm wide lenses when used on a full frame camera. Please note that we have more optional sizes available. This mask is attached to the MB-260 with magnets, gently pull the mask to the front to remove it.



Optional hood extender:

For people who want a bigger matte box, with a top flag, we have the Hood extender (0200-0261) available. This hood extender simply clips on the front of the matte box, without tools. You can convert your super compact MB-260 to a bigger matte box with top flag in seconds!



Other accessories and configuration chart:

Please see our website for more accessories and ready to use kits in the MB-260 system.
<https://www.vocas.com/matte-boxes/mb-260>

